



Maha Mini Streetlight

Outdoor Lighting Solutions

Product Features

- High system efficacy (114 lm/W)
- Intelligent and step dimming possibilities to meet project requirements
- Up to 8 different optical patterns available on request (PD0 standard)
- Tilttable head over 135° in 5° steps
- Replacement for 70W and 100W high pressure sodium lamp
- Reliable quality, manufacture capability, and global logistics by Delta Group 45-year establishment

Applications



Streets



Parks



Pedestrian

www.delta-emea.com



Smarter. Greener. Together.

	D02SEM100G	D02SEM200G	D02SEM300G	D02SEM400G	D02SEM500G	D02SEM600G
Type of Product	Street Lighting Solution					
Lumen Output (lm)	2950	3950	4950	5950	6950	8900
Input Voltage (V)	AC220~240V					
Power (W)	26	35	44	53	62	78
Efficacy (lm/W)	113		112		114	
CRI (Ra)	>70					
CCT (K)	4500					
Power Factor	>0.90					
Operating Temp (°C)	-35 °C / +40 °C					
Lens Options	PD0 standard (PDC, PDD, PDE, PDG, PDH, PDI, PDK on request)					
Lifetime	100.000 hr / L80					
Warranty	5 Years					
Protection	IP 65 / IK 08					
Weight (kg)	7.4	7.4	7.9	7.9	7.9	7.9
Accessories	DALI / Step dimming / 1-10V dimming					
HPS Replacement	70 W	70 W	70 W	100 W	100 W	100 W
Dimensions (mm)						
Photometry						
	PD0 4950 lm 4500 K C0.0-C180.0 C90.0-C270.0					
Housing	Grey RAL 9006. Black finish RAL 9005 available on request.					

Specifications are subject to change without notice.

Delta Electronics Europe

Zandsteen 15
 2132 MZ Hoofddorp, The Netherlands
 TEL: +31-20-655-0900
 FAX: +31-20-655-0999

For more product information and sales inquiries,
 please contact sleu@delta-europe.com
www.delta-emea.com/ledlighting

2016 ver.en-1.2

