




Wall mount



HEC1500PB series

Dimension drawing



Features

- ♦ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ♦ IP55 waterproof at external side.
- ♦ Precise temperature control.
- ♦ Earth-friendly refrigerant.
- ♦ Dry contact alarm output.

Design

- ♦ Compact size.
- ◆ Rated voltage at 48V.
- ♦ Built-in smart controller.
- ♦ High efficiency and reliable fan.
- ♦ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	700 x 500 x 200 (27.7 x 19.8 x 7.9)
Cooling capacity _{*Note}	W (BTU/hr)	1500 (5100)
Rated voltage	VDC	48
Operating current	Α	12.5
Operating voltage range	VDC	40 ~ 58
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	65.0
Weight	Kg (Lb)	28 (61.7)

* Note : L35/L35

^{*} Specifications are subject to change without notice.