



Rack Mount / Wall Mount









Features

- Quick heating
- Constant Air Flow
- ♦ 1U rack mount or Wall Mount
- ♦ High efficiency and reliable DC fan
- Overheat & short protect function
- 180 degree airflow blow for Rack Mount or 90 degree airflow blow for Wall Mount
- ♦ 2 sets in parallel optional for 19" rack use
- independence temperature sensor could mount anywhere of the cabinet

HEH100BB

Dimension drawing





Main feature	Unit	Specification
Outline Dimension	mm (inch)	44H x 220W x 177D (1.7 x 8.7 x 7)
Heating Capacity (note 1)	w	1000 ± 10%
Airflow rate	CFM	60 (typ.)
Rated voltage	VAC	220 (typ.)
Operating voltage range	VAC	200~240
Operating temperature range	°C	-40 ~ +65
Operating current	Α	5.4
Acoustic noise at 1M :	dB-A	65 (typ.)
Weight	Kg (lb)	1.25 (5.5)
Heating element	1	PTC
Ingress Protection rating	IP	IP20 (IEC60529)

Note 1: The heating capacity (w) is @20 °C (68°F) ambitent te