


Rack Mount





Airflow orientation

Features


- Quick heating
- **◆** Constant Air Flow
- ◆ 1U rack mount design
- ♦ High efficiency and reliable DC fan
- ♦ Overheat & short protect function
- ◆ 19"& 23"rack mount for choice
- **♦** Alarming Dry contact,
- ♦ LED indicator and Test button:

HEH100PB



Dimension drawing

- (1) Material: SGCC T=1.0mm (2) Finish: Powder paint 75~120um, Color RAL 7032 (3) Dimensional tolerance: ±1.0mm



Main feature	Unit	Specification	
Outline Dimension	mm (inch)	44H x 483W x 177D (1.7 x 19 x 7)	
Heating Capacity (note 1)	w	1000 ± 10%	
Airflow rate	CFM	55 (typ.)	
Rated voltage	VDC	48 (typ.)	
Operating voltage range	VDC	46~56	
Operating temperature range	°C	-40 ~ +65	
Operating current	Α	22	
Acoustic noise at 1M:	dB-A	65 (typ.)	
Weight	Kg (lb)	2.5 (5.5)	
Heating element	1	PTC	
Ingress Protection rating	IP	IP20 (IEC60529)	

Note 1: The heating capacity (w) is $\ @20\ ^{\circ}\mathbb{C}\,(68^{\circ}\mathbb{F})$ ambitent te