




Door mount



HET200VB series

Dimension drawing



HET200VB

Features

- ♦ IP55 waterproof at external side
- **FAN / TEC / Control fail alarm**
- ♦ Clear LED status indicator
- ♦ Standalone temperature control
- ♦ High efficiency and reliable fan modules

	Outline dimension	mm	400 H x 180 W x 209 D
	Weight	kg	9.0 ± 0.5
	Cooling capacity (△T =0℃)	W	200 (TYP.)
l	Heating capacity @ -40° C	W	225 (TYP.)
	Rated voltage	VDC	24 (TYP.)
	Operating voltage range	VDC	21~27
	Actuality Current	Α	12.2 (TYP.)
	Power Consumption	W	293
l	Operating temperature	°C	-40 ~ +65
	Internal airflow rate	CFM	100 (TYP.)
	External airflow rate		120 (TYP.)
	Acoustic noise at 1M :	dB-A	61.0 (TYP.)
	(Sound pressure)		64.0 (Max.)

* Specifications are subject to change without notice.

Design

- ♦ High efficiency of cooling & Heating
- ◆ Thermal electric cooling module
- ♦ Rated voltage at 24V
- ♦ Built-in controller