




Internal door mount



HEX150PB series

Dimension drawing



Features

- ♦ IP55 waterproof at external side
- ◆ "One touch" dry run test and dust cleaning
- ♦ Standalone temperature control
- ♦ Clear LED status indicator
- ◆ Dry contact alarm output

Design

- ◆ Air to air heat exchange
- ♦ Rated voltage at 48V
- Reduntant fan quantity design
- ♦ High efficiency and reliable fan
- ♦ Easy installation and maintenance

Main feature	Unit	Specification	
Dimension (H x W x D)	mm (inch)	640 x 550 x 278 (25 x 22 x 11)	
Cooling capacity _{*Note}	W/K (W/ °F)	110 (61)	150 (83)
Rated voltage	VDC	48	
Operating current	Α	2.6	5.8
Opearting power	W	125	279
Operating voltage range	VDC	40 ~ 60	
Operating temperature range	°C	-10 ~ +65	
Noise (1.5 meter)	dB-A	65.0	73.0
Weight	Kg (Lb)	20 (44)	

* Note : The cooling capacity (W/K , W/°C or W/°F) is defined as Q/ (TI-TA)

Q: Heat dissipation (W) from inside of cabinet

TI : Return temperature of internal air circuit (K , °C or °F)

TA: Ambient temperature of external air circuit (K, °C or °F)

^{*} Specifications are subject to change without notice.