



## Internal door mount



#### Features


- ♦ IP55 waterproof at external side
- ♦ Standalone temperature control
- RS-485 function (Optional)
- ♦ Clear LED status indicator
- ◆ Dry contact alarm output

### Design

- ◆ Air to air heat exchange
- ◆ Rated voltage at 48V
- ♦ High efficiency and reliable fan
- ♦ Easy installation and maintenance

# **HEX160PA** series

#### **Dimension drawing**



Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	1294 x 567 x 243 (51 x 23 x 10)
Cooling capacity <sub>*Note</sub>	<b>W/K (W/°</b> F)	160 (89)
Rated voltage	VDC	48
Operating current	Α	3.1
Opearting power	W	150
Operating voltage range	VDC	40 ~ 60
Operating temperature range	°C	-10 ~ +65
Noise (1.5 meter)	dB-A	65.0
Weight	Kg (Lb)	40 (88)

<sup>\*</sup> Note : The cooling capacity (W/K , W/°C or W/°F) is defined as  $\,$  Q/  $(T_{\Gamma}T_{A})$ 

Q : Heat dissipation (W) from inside of cabinet

T<sub>I</sub>: Return temperature of internal air circuit (K, °C or °F)

 $T_A$ : Ambient temperature of external air circuit (K , °C or °F)

<sup>\*</sup> Specifications are subject to change without notice.