




Internal door mount

HEX200PB series

Dimension drawing





Features

- ♦ IP55 waterproof at external side
- ♦ "One touch" dry run test and dust cleaning
- Standalone temperature control
- Clear LED status indicator
- Dry contact alarm output

Design

- ♦ Air to air heat exchange
- Rated voltage at 48V
- Reduntant fan quantity design
- High efficiency and reliable fan
- Easy installation and maintenance

Main feature	Unit	Specification	
Dimension (H x W x D)	mm (inch)	640 x 700 x 278 25 x 28 x 11	
Cooling capacity _{*Note}	W/K (W/° F)	145 (81)	200 (111)
Rated voltage	VDC	48	
Operating current	Α	2.6	7.9
Opearting power	w	125	380
Operating voltage range	VDC	40 ~ 60	
Operating temperature range	°C	-10 ~ +65	
Noise (1.5 meter)	dB-A	65.0	74.0
Weight	Kg (Lb)	24 (53)	

* Note : The cooling capacity (W/K , W/°C or W/°F) is defined as Q/ (TI-TA)

Q : Heat dissipation (W) from inside of cabinet

TI : Return temperature of internal air circuit (K , °C or °F)

- TA : Ambient temperature of external air circuit (K , °C or °F)
- * Specifications are subject to change without notice.