




External door mount



HEX200PC series

Dimension drawing



Features

- ♦ IP55 waterproof at external side
- ◆ "One touch" dry run test and dust cleaning
- ♦ Standalone temperature control
- ♦ Clear LED status indicator
- ◆ Dry contact alarm output

Design

- ◆ Air to air heat exchange
- ♦ Rated voltage at 48V
- ◆ Reduntant fan quantity design
- ♦ High efficiency and reliable fan
- ♦ Easy installation and maintenance

Main feature	Unit	Specification	
Dimension (H x W x D)	mm (inch)	690 x 700 x 242 (27 x 28 x 10)	
Cooling capacity _{∗Note}	W/K (W/ °F)	135 (75)	185 (103)
Rated voltage	VDC	48	
Operating current	Α	2.6	6.6
Opearting power	W	125	317
Operating voltage range	VDC	40 ~ 60	
Operating temperature range	°C	-10 ~ +65	
Noise (1.5 meter)	dB-A	65.0	74.0
Weight	Kg (Lb)	24 (53)	

* Note : The cooling capacity (W/K , W/°C or W/°F) is defined as Q/ (TI-TA)

Q: Heat dissipation (W) from inside of cabinet

TI: Return temperature of internal air circuit (K, °C or °F)

TA: Ambient temperature of external air circuit (K, °C or °F)

^{*} Specifications are subject to change without notice.