

External door mount



Features

- ♦ IP55 waterproof at external side.
- ♦ Standalone temperature control.
- RS-485 function (Optional).
- ♦ Dry contact alarm output.
- ♦ Clear LED status indicator.


Design


- Narrow size.(width only 425mm)
- ♦ Rated voltage at 48V.
- ♦ Built-in smart controller.
- High efficiency and reliable fan.
- Easy installation and maintenance.
- ◆ Refrigerant R134a used.


HEX200PE



Dimension drawing







Main feature	Unit	Specification
Dimension (H x W x D) (Doesn't contain flange)	mm (inch)	1330 x 425 x 230 (52.4 x 16.7 x 9.1)
Cooling capacity	W/K	200
Rated voltage	VDC	48
Operating current	Α	8.4
Operating voltage range	VDC	40 ~ 60
Operating temperature range	ĉ	-10 ~ +65
Noise (1.0 meter)	dB-A	61.5
Weight	Kg (Lb)	42 (92.6)

* Specifications are subject to change without notice.