




## **Door Mounting type**



## HEX050PA series

**Dimension drawing** 



## **Features**

- ♦ IP55 waterproof at external side
- ◆ "One touch" dry run test and dust cleaning
- ♦ Optional communication function design
- ◆ Easy installation and maintenance from internal side
- ◆ Clear LED status indicator
- ♦ High efficiency and reliable fan modules

## Design

- ◆ Air to air heat exchange
- ◆ Door mounted
- ◆ Rated voltage at 48V
- Complete airtight design for outdoor application
- Drainage hole in the bottom
- ◆ Reduntant fan quantity design

Main feature	Unit	Specification
Dimension (H x W x D)	mm	500 x 445 x 152
Cooling capacity	W/K	50 (MAX.) <sub>*Note</sub>
Rated voltage	Vdc	48 (TYP.)
Operating voltage range	Vdc	40 ~ 60
Rated current	Α	1.44 (MAX.)
Power consumption	w	70.0 (MAX.)
Operating temperature range	°C	-10 ~ +65
Internal airflow	CFM	210
External airflow	CFM	210
Weight	Kg	10.0

\* Note : The cooling capacity (W/K OR W/°C) is defined as  $\, Q/ \, (T_I - T_A) \,$ 

Q: Heat dissipation (W) from inside of cabinet

T<sub>I</sub>: Return temperature of internal air circuit (K OR °C)

T<sub>A</sub>: Ambient temperature of external air circuit (K OR °C)

<sup>\*</sup> Specifications are subject to change without notice.