

Door Mounting type



Features


- ♦ IP55 waterproof at external side
- ◆ "One touch" dry run test and dust cleaning
- Optional communication function design
- Easy installation and maintenance from internal side
- ♦ Clear LED status indicator
- High efficiency and reliable fan modules

Design

- Air to air heat exchange
- ◆ Door mounted
- ◆ Rated voltage at 48V
- Complete airtight design for outdoor application
- ◆ Drainage hole in the bottom
- Reduntant fan quantity design

HEX200PC series

Dimension drawing



	1	
Main feature	Unit	Specification
Dimension (H x W x D)	mm	690 x 700 x 242
Cooling capacity	W/K	200 (MAX.) *Note
Rated voltage	Vdc	48 (TYP.)
Operating voltage range	Vdc	40 ~ 60
Rated current	Α	7.92 (MAX.)
Power consumption	W	380.2 (MAX.)
Operating temperature range	°C	-10 ~ +65
Internal airflow	CFM	610
External airflow	CFM	550
Weight	Kg	24.0

* Note : The cooling capacity (W/K OR W/°C) is defined as Q/ (T_I-T_A)

Q : Heat dissipation (W) from inside of cabinet

T_I: Return temperature of internal air circuit (K OR °C)

T_A: Ambient temperature of external air circuit (K OR °C)

* Specifications are subject to change without notice.