

Door Mounting type



Features


- IP55 waterproof at external side
- "One touch" dry run test and dust cleaning
- Optional communication function design
- Easy installation and maintenance from internal side
- Clear LED status indicator
- High efficiency and reliable fan modules


Design

- Air to air heat exchange
- Door mounted
- Rated voltage at 48V
- Complete airtight design for outdoor application
- Drainage hole in the bottom
- Redantant fan quantity design

HEX260PA series

Dimension drawing





External

Internal

Main feature Specification Unit Dimension (H x W x D) 1400 x 650 x 260 mm 260 (MAX.) *Note **Cooling capacity** W/K **Rated voltage** Vdc 48 (TYP.) 40 ~ 60 Operating voltage range Vdc **Rated current** Α 12.0 (MAX.) 576.0 (MAX.) **Power consumption** W -10 ~ +65 Operating temperature range °C Internal airflow CFM 940 **External airflow** CFM 640 Weight 37 Kg

260

尾

* Note : The cooling capacity (W/K OR W/°C) is defined as Q/ (T_I-T_A)

Q : Heat dissipation (W) from inside of cabinet

T_I: Return temperature of internal air circuit (K OR °C)

T_A : Ambient temperature of external air circuit (K OR °C)