



# Wall mount



#### **Features**


- ◆ Reliable and energy efficient thermal solutions.
- Energy efficient fans and effective compressor.
- ◆ IP55 waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.

## Design

- ♦ Slim design.
- Rated voltage at 48V.
- Built-in smart controller.
- ♦ High efficiency and reliable fan.
- Easy installation and maintenance.

## HEC0700PA series

### **Dimension drawing**



Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	545 x 320 x 170 (21.5 x 12.6 x 6.7)
Cooling capacity <sub>*Note</sub>	W (BTU/hr)	700 (2300)
Rated voltage	VDC	48
Operating current	Α	3.5
Operating voltage range	VDC	42 ~ 58
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	65.0
Weight	Kg (Lb)	16 (35.3)

\* Note : L35/L35

<sup>\*</sup> Specifications are subject to change without notice.