





Wall mount



Dimension drawing







Features

- Reliable and energy efficient thermal solutions.
- Energy efficient fans and effective compressor.
- IP55 waterproof at external side.
- Precise temperature control.
- Earth-friendly refrigerant.
- Dry contact alarm output.

Design

- ♦ Compact size.
- Rated voltage at 48V.
- ♦ Built-in smart controller.
- High efficiency and reliable fan.
- Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	700 x 500 x 200 (27.7 x 19.8 x 7.9)
Cooling capacity-Note	W (BTU/hr)	800 (2720)
Rated voltage	VDC	48
Operating current	Α	3.7
Operating voltage range	VDC	40 ~ 58
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	65.0
Weight	Kg (Lb)	28 (61.7)

* Note : L35/L35

* Specifications are subject to change without notice.