



Wall mount



Features


- ♦ Reliable and energy efficient thermal solutions.
- Energy efficient fans and effective compressor.
- IP55 waterproof at external side.
- ◆ Precise temperature control.
- ♦ Earth-friendly refrigerant.
- Dry contact alarm output.

Design

- Slim design.
- Rated voltage at 48V.
- ♦ Built-in smart controller.
- ♦ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

HEC0800PC series

Dimension drawing



Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	796 x 383 x 160 (31.3 x 15.0 x 6.4)
Cooling capacity _{*Note}	W (BTU/hr)	800 (2720)
Rated voltage	VDC	48
Operating current	Α	3.8
Operating voltage range	VDC	42 ~ 58
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	55.0
Weight	Kg (Lb)	27 (59.5)

* Note : L35/L35

^{*} Specifications are subject to change without notice.