



# Door mount



#### **Features**


- ♦ IP55 waterproof at external side
- ◆ FAN / TEC / Control fail alarm
- **♦** Clear LED status indicator
- **♦** Standalone temperature control
- ♦ High efficiency and reliable fan modules

### Design

- ♦ High efficiency of cooling & Heating
- ◆ Thermal electric cooling module
- **♦** Rated voltage at 48V
- ♦ Built-in controller

## HET200PC series

### **Dimension drawing**



	•	
Main feature	Unit	Model Number
		HET200PC
Outline dimension	mm	400 H x 180 W x 169 D
Weight	Kg	6.0 ± 0.5
Cooling capacity (△T =0° C)	W	200
Heating capacity @-40° C	W	225
Rated voltage	VDC	48 (TYP.)
Operating voltage range	VDC	40-56
Actuality Current	Α	6.1 (TYP.)
Power Consumption	w	293
Operating temperature	°Ç	-40~55
Internal airflow rate	CFM	100 (TYP.)
External airflow rate		120 (TYP.)
Acoustic noise at 1M :	dB-A	61.0 dB-A(Typ.)
(Sound pressure)		65.0(Max.)

<sup>\*</sup> Specifications are subject to change without notice.