




Door mount



HET200VC series

Dimension drawing



Features

Main feature Unit

HET200VC

- ♦ IP55 waterproof at external side
- ◆ FAN / TEC / Control fail alarm
- ♦ Clear LED status indicator
- Standalone temperature control
- ♦ High efficiency and reliable fan modules

Outline dimension	mm	400 H x 181 W x 169 D
Weight	Kg	6.0 ± 0.5
Cooling capacity ($ riangle T$ =0 $^\circ \!\!\! \mathbb{C}$)	w	200
Heating capacity @-40° C	w	225
Rated voltage	VDC	24 (TYP.)
Operating voltage range	VDC	20-28
Actuality Current	Α	12A(TYP.)
Power Consumption	w	288
Operating temperature	°C	-40~55
Internal airflow rate	CFM	85 (TYP.)
External airflow rate		115 (TYP.)
Acoustic noise at 1M :	dB-A	61.0 dB-A(Typ.)
(Sound pressure)		65.0(Max.)

* Specifications are subject to change without

notice.

Design

- ♦ High efficiency of cooling & Heating
- ♦ Thermal electric cooling module
- ♦ Rated voltage at 24V
- Built-in controller