



UL file NO.: E358666

Wall mount




HEH100BA series

Dimension drawing

NOTE :

- (1) Material : AL T=1.5mm
- (2) Finish : Powder paint 75~120um, Color 7035
- (3) Dimensional tolerance : $\pm 1.0\text{mm}$



Features

- ◆ Quick heating
- ◆ Constant Air Flow
- ◆ Dry contact control
- ◆ Component fail alarm
- ◆ Compact design
- ◆ Soft Start
- ◆ High efficiency and reliable fan
- ◆ Easy installation

Main feature	Unit	Model Number
		HEH100BA
Outline dimension	mm	235 H x 185 W x 58 D
Weight	kg	1.5 \pm 0.5
Heating Capacity	W	1000 \pm 10%
Rated voltage	Vac	220 (typ.)
Operating voltage range	Vac	200-240
Operating status	N/A	LED indicator
Fan /Heater fail alarm	N/A	Dry contact output
Inrush current	A	10

* Specifications are subject to change without notice.