


Wall mount



HEC2000BAS series

Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions
- ◆ Energy efficient fans and effective compressor
- ◆ IP55 waterproof at external side
- ◆ Precise temperature control
- ◆ Earth-friendly refrigerant (GWP <7)
- ◆ Dry contact alarm output
- ◆ Remote control function

Design

- ◆ Compact size
- ◆ Rated voltage at 200 ~ 240 VAC
- ◆ Built-in smart controller
- ◆ High efficiency and reliable fan
- ◆ Easy installation and maintenance

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	1200 x 450 x 230 (47.24 x 17.71 x 9.05)
Cooling capacity*Note	W (BTU/hr)	2000 (6824)
Rated voltage	VAC	200 ~ 240
Operating current	A	3.5
Operating voltage range	VAC	180 ~ 264
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	67
Weight	Kg (Lb)	41.5 (91.5)

* Note : L35/L35

* Specifications are subject to change without notice.