


Wall mount

HEC2000FFA series

Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ◆ IP55 waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.
- ◆ Heating function.

Design

- ◆ Compact size.
- ◆ Rated voltage at 230 VAC.
- ◆ Built-in smart controller.
- ◆ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	746 x 446 x 200 (29.4 x 17.6 x 7.9)
Cooling capacity*Note	W (BTU/hr)	2000 (6820)
Rated voltage	VAC	230
Operating power	W	730
Operating voltage range	VAC	196 ~ 264
Heating capacity	W (BTU/hr)	1000 (3040)
Operating temperature range	°C	-40 ~ +55
Noise (1.0 meter)	dB-A	65.0
Weight	Kg (Lb)	37.0 (81.6)

* Note : L35/L35

* Specifications are subject to change without notice.