

Picture	Part number	Dimension (mm)	Operating Voltage Range (VDC)	Voltage (VDC)	Current (A)	Power (W)	Speed (RPM)	Noise (dB-A)	Air Flow		Air Pressure	
	AUB0405HD	40x40x20	4.0 ~ 5.5	5.0	0.13	0.65	6000	20.5	7.770	CFM	0.156	inchH ₂ O
	AUB0412HD-00		6.0 ~ 13.2	12.7	0.05	0.64			0.220	M ³ /min	3.960	mmH ₂ O
	AUB0612HHB-A	60x60x15	7.0 ~ 13.8	12.0	0.13	1.56	4500	33.0	23.370	CFM	0.190	inchH ₂ O
									0.662	M ³ /min	4.830	mmH ₂ O
	AUB0712HH-C	70x70x25	5.0 ~ 13.2	12.0	0.25	3.00	4500	40.5	36.600	CFM	0.288	inchH ₂ O
									1.037	M ³ /min	7.320	mmH ₂ O
	AUB0812H-E	80x80x25.4	5.0 ~ 13.2	12.0	0.23	2.76	3900	37.5	50.150	CFM	0.239	inchH ₂ O
									1.421	M ³ /min	6.080	mmH ₂ O
	AUB0912HJ-00	92x92x25	10.8 ~ 13.2	12.0	0.35	4.20	4600	45.0	69.020	CFM	0.407	inchH ₂ O
									1.955	M ³ /min	10.340	mmH ₂ O
	ASB1212LE-00	119x119x38	10.8 ~ 13.2	12.0	0.16	1.92	2000	35.5	80.010	CFM	0.150	inchH ₂ O
	AFB1212LE-02		7.0 ~ 13.2						2.266	M ³ /min	3.800	mmH ₂ O
	BUB0612MJ-00	60x60x23	5.0 ~ 13.2	12.0	0.16	1.92	4400	35.0	8.164	CFM	0.669	inchH ₂ O
									0.231	M ³ /min	17.000	mmH ₂ O
	BUB0612HJ-01	60x60x23	10.8 ~ 13.2	12.0	0.42	5.04	5800	42.0	12.016	CFM	1.378	inchH ₂ O
									0.340	M ³ /min	35.000	mmH ₂ O
	BUB0712HJ-00	70x70x25	4.0 ~ 13.2	12.0	0.42	5.04	4650	45.5	14.090	CFM	1.140	inchH ₂ O
									0.399	M ³ /min	29.000	mmH ₂ O
	BCB0712GF-00	70x70x28	10.8 ~ 13.2	12.0	1.45	17.40	8600	60.0	30.392	CFM	4.528	inchH ₂ O
									0.860	M ³ /min	115.000	mmH ₂ O
	BUB0712HD-SM	75x75x20	10.8 ~ 12.6	12.0	0.26	3.12	3800	41.5	10.210	CFM	0.831	inchH ₂ O
									0.289	M ³ /min	21.100	mmH ₂ O
	BFB0812HHB	80x80x15	10.0 ~ 12.8	12.0	0.40	4.80	5500	50.0	9.180	CFM	1.240	inchH ₂ O
									0.260	M ³ /min	31.600	mmH ₂ O
	BCB0812VN-00	80x80x26	7.0 ~ 12.8	12.0	1.10	13.20	7000	60.0	24.738	CFM	3.937	inchH ₂ O
									0.700	M ³ /min	100.000	mmH ₂ O
	BUB0812HN-00	80x80x28	10.8 ~ 13.2	12.0	0.50	6.00	4300	44.5	18.840	CFM	1.350	inchH ₂ O
									0.534	M ³ /min	34.300	mmH ₂ O
	BUB0912HE-00	94x82x39	12.0 ~ 18.0	14.4	2.90	13.20	19500	73.5	31.000	CFM	13.380	inchH ₂ O
									0.877	M ³ /min	340.000	mmH ₂ O
	BUB0812MB-00	94x90x16	10.8 ~ 12.6	12.0	0.40	4.80	4300	52.0	16.910	CFM	0.960	inchH ₂ O
									0.479	M ³ /min	24.480	mmH ₂ O
	BFB1012UH-B	97x94x25	12.0 ~ 16.8	14.2	2.15	30.53	7000	68.0	36.940	CFM	4.764	inchH ₂ O
									1.046	M ³ /min	121.000	mmH ₂ O
	BFB1012EH-C	97x94x33	10.8 ~ 14.0	12.0	1.97	23.64	5800	62.0	45.490	CFM	3.694	inchH ₂ O
									1.288	M ³ /min	93.830	mmH ₂ O
	BFB1012EF-00	97x94x33	10.8 ~ 12.6	12.0	5.00	60.00	7500	69.0	56.080	CFM	6.903	inchH ₂ O
									1.588	M ³ /min	175.400	mmH ₂ O
	BFB1212MF-02	120x120x32	7.0 ~ 13.2	12.0	0.55	6.60	2300	48.5	26.900	CFM	0.716	inchH ₂ O
									0.762	M ³ /min	18.200	mmH ₂ O
	BUB1212MF-00	120x120x32	5.0 ~ 13.2	12.0	0.45	5.40	2500	48.5	26.900	CFM	0.716	inchH ₂ O
									0.762	M ³ /min	18.200	mmH ₂ O