

Picture	Part number	Dimension (mm)	Operating Voltage Range (VDC)	Voltage (VDC)	Current (A)	Power (W)	Speed (RPM)	Noise (dB-A)	Air Flow		Air Pressure	
	BFB0712HJ-01	75x75x25	7.0 ~ 13.2	12.0	0.30	3.60	4000	51.0	13.840 CFM 0.392 M ³ /min		0.750 inchH ₂ O 19.050 mmH ₂ O	
	BFB1012M-01	98x96x33	6.0 ~ 13.2	12.0	0.42	5.04	2700	49.0	26.240 CFM 0.743 M ³ /min		0.596 inchH ₂ O 15.130 mmH ₂ O	
	BFB1212VF-00	120x120x32	10.8 ~ 13.2	12.0	0.80	9.60	2800	54.0	32.490 CFM 0.920 M ³ /min		1.063 inchH ₂ O 27.000 mmH ₂ O	
	BUB1212MF-00	120x120x32	7.0 ~ 13.2	12.0	0.45	5.40	2500	48.5	26.900 CFM 0.762 M ³ /min		0.716 inchH ₂ O 18.200 mmH ₂ O	