




Picture	Part number	Dimension (mm)	Operating Voltage Range (VDC)	Voltage (VDC)	Current (A)	Power (W)	Speed (RPM)	Noise (dB-A)	Air Flow	Air Pressure
	ASB0250LP-00	20x20x6.3	4.5 ~ 5.5	5.0	0.03	0.15	7000	29.0 @ 0.05m	0.424 CFM 0.012 M ³ /min	0.053 inchH ₂ O 1.350 mmH ₂ O
	BSB0205HP-01FEY	20x20x6.3	3.0 ~ 5.5	5.0	0.08	0.40	13000	25.0	0.212 CFM 0.006 M ³ /min	0.142 inchH ₂ O 3.600 mmH ₂ O
	ASB0205HA-00	20x20x10	3.0 ~ 5.5	3.5	0.04	0.14	7000	17.0 @ 0.2m	0.601 CFM 0.017 M ³ /min	0.052 inchH ₂ O 1.320 mmH ₂ O