



MH09012RA







• Housing: VHR-5N

Pin 1: Red, Vm (12 VDC)

Pin 2: Yellow, Vsp (0 ~ 5 VDC)

Pin 3: Blue, F/G Signal Output (12 pulses/rev.)

Pin 4: Empty

Pin 5: Black, GND

• Safety: UL / CE

Unit: mm

Model No.	Working Voltage (VDC)	Rated Voltage (VDC)	Pulse / Revolution	Rated Load Speed (rpm)	Rated Torque (N-cm)	Rated Current (A)	Rated Output Power (W)	No Load Noise (dB(A))
MH09012RA-N0400	10.8~13.2	12	12	1500	2.6	0.55	4	< 40
MH09012RA-N1500	10.8~13.2	12	12	1500	9.55	1.80	15	< 40

- Noise measuring condition: shaft horizontal / mic. 15 cm away from motor
- All readings are typical values at rated voltage.
- Specifications are subject to change without notice.

Delta Confidential