

# 60 W/20 W USB Socket Outlets

Empowering a high efficient, convenient charging



# Charging Everywhere Makes Life Easier



## Home Decor

Best Choice for Interior Design

**Sites** Living room, bedroom, study



## Furniture

Upgrade Your Smart Home

**Sites** Desk, side table, bedside, and more



## Commercial

Charge Efficiently, Work Vigorously

**Sites** Office, meeting room, hotel, coffee house



## Public Space

Charge Whenever Needed

**Sites** Airport, train / subway / bus station, library

### High Wattage, High Efficiency

- USB Dual-Ports, with a maximum 60W power output
- 0%-50% fast charging for iPhone 15 large capacity models within 30 minutes
- Applicable to mobile phones, laptops, and other electrical devices

### Safety Assurance

- 10,000 mating cycles
- Compliant with CB, UL/CSA, BSMI, PSE, LPS, UL94V-0 and other safety and fire prevention standards
- Complete compatibility testing to charge electric devices of different brands
- 5 major circuit protections\*

\* Overcurrent protection (OCP), Overvoltage protection (OVP), Overtemperature protection (OTP), Overload protection (OPP), Output short circuit protection (SCP)

### Easy Installation

- Modular design for sockets of various brands
- Flexible combination with USB sockets, AC outlets, and light switches (up to three)
- Compatible with different socket clips for easy installation

### Environmental-friendly

- Connector-free design to be more eco-friendly
- Industry-leading 92% energy conversion efficiency to reduce energy waste
- Adopts automated manufacturing and recyclable materials for a more sustainable future

## Products

		60 W USB-C+C Socket Outlets	60 W USB-A+C Socket Outlets	20 W USB-A+C Socket Outlets
Socket Outlets				
Socket Outlets				
Port		USB-C + C	USB-A + C	USB-A + C
Depth		44.1 mm	43.2 mm	43.7 mm
AC Input		100-132 V <sub>AC</sub> / 1.6 A 50-60 Hz		100 - 132 V <sub>AC</sub> / 0.8 A 50 - 60 Hz
DC Output	Single Port	Max. 60 W (USB - C) environment temp. 35°C	Max. 60 W (USB - C)	Max. 20 W (USB - C)
	Dual Port	30W (USB - C)+30W (USB - C) or 45W (USB - C)+10W (USB - C)	36 W (USB - C) 12 W (USB - A)	7.5 W (USB - C) 7.5 W (USB - A)
Power Rating		USB - C/C: 5 V 3 A/9 V 3 A/ 15 V 3 A/ 20 V 3 A	USB - C: 5 V 3 A/9 V 3 A/15 V 3 A/20 V 3 A, USB - A: 5 V 2.4 A	USB - C: 5 V 3 A/9 V 2.22 A/12 V 1.67 A USB - A: 5 V /2.4 A
U.S. Department of Energy (DOE)		VI		
Safety		CB, UL/CSA, BSMI, PSE, IEC 62368-1		
Build in Protection		Overcurrent protection (OCP), Overvoltage protection (OVP), Overtemperature protection (OTP), Overload protection (OPP), Output short circuit protection (SCP)		
Protocol		PD3.0, BC1.2, Apple Mode (2.4 A)		
Color		White, Black	White, Grey	

## Optional Outlet Covers



Lily-White

Elegant Silver

Royal Black



[https://www.deltaww.com/pd\\_charging/en/](https://www.deltaww.com/pd_charging/en/)

Jan. 2024 - All information and specifications are subjected to change without prior notice.