

60 W/20 W USB Socket Outlets

Empowering a high efficient, convenient charging



Charging Everywhere Makes Life Easier



Home Decor

Best Choice for Interior Design

Sites Living room, bedroom, study



Furniture

Upgrade Your Smart Home

Sites Desk, side table, bedside, and more



Commercial

Charge Efficiently, Work Vigorously

Sites Office, meeting room, hotel, coffee house



Public Space

Charge Whenever Needed

Sites Airport, train / subway / bus station, library

High Wattage, High Efficiency

- USB Dual-Ports, with a maximum 60W power output
- 0%-50% fast charging for iPhone 15 large capacity models within 30 minutes
- Applicable to mobile phones, laptops, and other electrical devices

Safety Assurance

- 10,000 mating cycles
- Compliant with CB, UL/CSA, BSMI, PSE, LPS, UL94V-0 and other safety and fire prevention standards
- Complete compatibility testing to charge electric devices of different brands
- 5 major circuit protections*

* Overcurrent protection (OCP), Overvoltage protection (OVP), Overtemperature protection (OTP), Overload protection (OPP), Output short circuit protection (SCP)

Easy Installation

- Modular design for sockets of various brands
- Flexible combination with USB sockets, AC outlets, and light switches (up to three)
- Compatible with different socket clips for easy installation

Environmental-friendly

- Connector-free design to be more eco-friendly
- Industry-leading 92% energy conversion efficiency to reduce energy waste
- Adopts automated manufacturing and recyclable materials for a more sustainable future

Products

		60 W USB-C+C Socket Outlets	60 W USB-A+C Socket Outlets	20 W USB-A+C Socket Outlets
Socket Outlets				
Port		USB-C + C	USB-A + C	USB-A + C
Depth		44.1 mm	43.2 mm	43.7 mm
AC Input		100-132 V _{AC} / 1.6 A 50-60 Hz		100 - 132 V _{AC} / 0.8 A 50 - 60 Hz
DC Output	Single Port	Max. 60 W (USB - C) environment temp. 35°C	Max. 60 W (USB - C)	Max. 20 W (USB - C)
	Dual Port	30W (USB - C)+30W (USB - C) or 45W (USB - C)+10W (USB - C)	36 W (USB - C) 12 W (USB - A)	7.5 W (USB - C) 7.5 W (USB - A)
Power Rating		USB - C/C: 5 V 3 A/9 V 3 A/ 15 V 3 A/ 20 V 3 A	USB - C: 5 V 3 A/9 V 3 A/15 V 3 A/20 V 3 A, USB - A: 5 V 2.4 A	USB - C: 5 V 3 A/9 V 2.22 A/12 V 1.67 A USB - A: 5 V /2.4 A
U.S. Department of Energy (DOE)		VI		
Safety		CB, BSMI, PSE, UL / CSA 62368		
Build in Protection		Overcurrent protection (OCP), Overvoltage protection (OVP), Overtemperature protection (OTP), Overload protection (OPP), Output short circuit protection (SCP)		
Protocol		PD3.0, BC1.2, Apple Mode (2.4 A)		
Color		White, Black	White, Grey	

Optional Outlet Covers



Lily-White

Elegant Silver

Royal Black



Join us Learn more



🌐 https://www.deltaww.com/pd_charging/

✉ WS-Service@deltaww.com

May. 2024 - All information and specifications are subjected to change without prior notice.