



LED Panel Lighting

Albedo Eco Back-Lit (BL) Radiant

Energy-efficient & power adjustable

- Slim and lightweight panel for easy installation and maintenance
- UGR19 with micro prismatic diffuser
- System efficiency up to 140 lm/W
- Adjustable power switch on the driver
- Best flicker free lighting
- Simple Plug & Play connector
- 5 years warranty

Applications



Offices



Commercial



Retail



Healthcare

	LSHD05PACR6340-ML	LSHD05PACRG340-ML		
Lumen Output (lm)	3300 / 3900 / 4500 / 5000			
Power (W)	24 / 28 / 32 / 36 (switchable)			
Efficacy (lm/W)	up to 140			
CRI	>80			
CCT	4000K			
Operating Temperature	- 20° to +40°C			
Lifetime	L80B10> 50 000h at Ta=25°C			
Input Voltage	220-240 V			
UGR	<19			
Ingress Protection	IP20 (back side) / IP40 (room side)			
Impact Resistance	IK02			
Power Factor	>0.9			
Electrical Safety Class	Class II			
Photo-biological Safety	RG0			
Color Tolerance (MacAdam)	< 4 SDCM			
Weight (kg)	1.8	2		
Product Dimension (mm)	595 * 595 * 33	620* 620 * 33		
Control Interface	ON/OFF - DALI 2 (optional)			
Accessories & options	Safety cable (included) Suspension kit LSHD05PAC0022 Surface mounting frame 600*655*67 mm LSHD05PAC0021 Surface mounting frame 624*680*67 mm LSHD05PAC0027 Emergency kit LSHD05PAC0024 Recessed mounting frame 625*625*40 mm LSHD05PAC0028 Recessed mounting frame 650*650*40 mm LSHD05PAC0029			
Dimension				
Photometry				
Remark	More technical information : Glow Wire Test at 650°C / 1kV Surge Protection / Flickering <3% at 100Hz / THD<20%			

Delta Electronics (Netherlands) B.V.

Zandsteen 15, 2132 MZ Hoofddorp, The Netherlands

E: sleu@deltaww.com

T: +31-20-655-0900