



High-bay LED Lighting

Cerratto Series

Light weighted with high performance

- Glare free (UGR <22)
- Convenient installation with options for hook, bracket
- Ultra-light weight (~3.2Kg)
- Elegant typical fixture shape

Applications



Industrial



Warehouse



General
Manufacturing

www.deltaww.com



	LCDB84900E	LCDBD4900E	LCDBF4900E
Lumen Output	12,000 lm	18,400 lm	20,900 lm
Input Voltage	220-240V		
Efficacy	141 lm/w	142 lm/w	135 lm/w
Power	85 W	130 W	155 W
CRI	≥80 Ra		
CCT(K)	4000 (5000K Available)		
Operating Temperature	Ta : -40~55+°C		Ta : -40~50+°C
	Thermal foldback feature reduces lumen output for temperatures above Ta Max		
Power Factor	≥0.9		
Beam Angle	90°		
Ingress Protection/ Impcat Resistance	IP66/IK10		
Weight (kg)	3.2KG		
Control Interface	0-10V		
Mounting	Hook / Wall Mount		
Accessories & options	U-Bracket		
Photometry			
Product Dimension			
Remarks	Product codes and lumen output ranges are subject to change when other CCT applies.		

For more product information and sales inquiries, please contact: sleu@deltaww.com



Delta Electronics Europe
Zandsteen 15
2132 MZ Hoofddorp, The Netherlands
TEL: +31-20-655-0900
FAX: +31-20-655-0999



buildings.deltaww.com

All specifications are subject to change without notice. Copyright © Delta Electronics, Inc. All rights reserved.

Cerratto Series_EMEA_202306