



70" DLP LED Video Wall Cubes


Product Features

- Long-Lasting LED Light Engine
- Superior Color Uniformity
- Six-Axis Adjustment For Perfect Alignment
- Auto Color Calibration
- Advanced Optical & Screen Design
- Redundant Power Supply Module
- Wireless Diagnostics and Control
- Motorized 6-Axis Adjustment

www.deltadisplays.com



Smarter. Greener. Together.



Specifications

Model		DVS-7080R9 DO CB	
Display Capabilities			
Native Resolution	Full HD , 1,920 x 1,080		
Display Technology	1-Chip DLP		
Brightness On Screen (Nits)	XPS Screen	Eco	151
		Normal	383
		Bright	423
Dynamic Contrast	1,200,000 : 1		
White Point	3,200K , 6,500K , 7,500K and 9,300K		
Uniformity	> 96%		
System Adjustment - Optional	Auto Color Sensor Module		
	Motorized 6-Axis Adjustment		
Screen			
Screen Dimension (W X H)	1,550.0 x 872.0 mm		
Screen Type	XPS		
Screen Gap	< 0.1 mm		
Color Stability	Self Calibrating With Color Sensor		
Half Gain Angle (H / V)			
Horizontal	35°		
Vertical	27°		
Light Source			
Lamp Type	LED (RGB) , 6 x Redundancy for Each of 3 LED's		
Estimated Lamp Life	> 60,000 hrs , > 100,000 hrs (Eco)		
Operation			
Operating Temperature	5°C - 40°C (41°F - 104°F)		
Non-Operating Temperature	-20 °C - 60 °C (-4°F - 140°F)		
Humidity	10% - 90% , Non-Condensing		
Power Requirement			
Input Voltage	AC 90 - 240V @50/60Hz		
Consumption (Eco , Typ , Max)	150W , 225W , 270W		
Power Supply - Optional	Redundant Power Supply Module		
Mechanical			
Dimensions (W x H x D)	1,552.0 x 1,157.0 x 1,120.0 mm (61.0 x 45.6 x 44.1")		
Weight	Rear Access < 100KG (220 lb)		
Interface			
Standard Inputs	Analog D-Sub 15pin	Digital DVI-I	
	HDMI	Component Video BNC	
	CVBS BNC	5BNC (RGBHV or YPbPr)	
Optional Inputs	Display Port	3G-SDI	
	S-Video		
Standard Outputs	Digital DVI-D		
Input Frequency	24 – 62 Hz		
Signal Processing	Loop -Through (DVI , CVBS) Free Scaling		
Control			
Communication	RS-232 Port	RS-422 Port	
	IR Receiver	RJ-45 Ethernet	
IP Control System - Optional	DVSWeb Control System Software		

*All specifications are subject to change without prior notice.

Ver: 03. 2014

Delta Group website :

www.deltaww.com

Product website :

www.deltadisplays.com

Contact E-mail :

VW.Sales@deltadisplays.com

Europe

FRANCE

Delta Electronics (France) S.A.
ZI du bois Chaland 2 15 rue des
Pyrénées, Lisses, 91056 Evry
Cedex, France

NETHERLANDS

Delta Electronics Europe
Zandsteen 15, 2132 MZ
Hoofddorp,
The Netherlands

SLOVAKIA

Delta Electronics (Slovakia) s.r.o.
Priemyselna ulica 4600/1
018 41 Dubnica nad Vahom,
Slovakia

North America

USA/ FREMONT

Delta Products Corporation
4405 Cushing Parkway,
Fremont, CA 94538, U.S.A.

USA/ PORTLAND

Delta Products Corporation
1600 NW Compton Drive,
Suite 100, Beaverton OR 97006,
U.S.A.

Asia

TAIWAN

Delta Electronics, Inc.
186 Ruey Kuang Road, Neihu,
Taipei 11491, Taiwan

KOREA

Delta Electronics (Korea) Inc.
234-9, Duck soo Building 7F,
Nonhyun-dong, Kangnam-Gu,
Seoul, Korea 135-010

JAPAN

Delta Electronics (Japan) Inc.
Delta Shibadaimon Building,
2-1-14 Shibadaimon, Minato-Ku,
Tokyo, 105-0012, Japan

THAILAND

Delta Electronics (Thailand) PCL.
909 Soi 9, E.P.Z., Bangpoo
Industrial Estate, Moo 4, Pattana
1 Rd., T.Prakasa, A.Muang
Samutprakarn 10280, Thailand

INDIA

Delta India Electronics Pvt. Ltd.
Plot No 43, Sector 35, HSIDC,
Gurgaon 122001, Haryana,
India

CHINA

Delta Electronics (Jiang Su) Ltd.
1688 Jiangxing East Road,
Wujiang
Economic Development Zone,
Wujiang City, Jiang Su
Province, China

SINGAPORE

Delta Electronics (Singapore)
1, Kaki Bukit Road 1, #03 -29,
Enterprise One, Singapore
415934

