







1. INPUT	
Phase	1-Phase L-N Wiring
Voltage	200-240 Vac, 50/60 Hz
Current	32A (CE, UKCA) / 24A (UL)
Input Plug	IEC60309(2P+E), 6H, 32A (CE) / 30A (UL)
Input Cord	3,000±50mm(4mm ² /11AWGx3C)
2. OUTPUT	
Outlets	(36) IEC60320-C13+(6) IEC60320-C19
Protection	Circuit breaker - 240Vac/20A, 10KAIC, 1 Pole (2)
3. FEATURES	
Metering	Power metering for input and branch
Switching	N/A
Network Monitoring	HTTPs, SNMP

NOTE:
1. All dimension are in millimeters[inches].
2. Bracket kits to mount are available as options.

		台達電子工業股份有限公司 DELTA ELECTRONICS, INC.	
Drawn: Jackow Chen		Design: Jackow Chen	
 THIRD ANGLE PROJECTION	A3 SIZE		Description: PHYSICAL DIMENSION
	Part No.: PDUA117BSA23500		REV. 00
SHEET 1 OF 2		ISSUE DATE: 03/24/2023	



NOTE:

- 1. Please see product documentation for further information.
- 2. This drawing depicts the line connections and is not representative of the physical layout.

		台達電子工業股份有限公司 DELTA ELECTRONICS, INC.	
Drawn: Carol Li		03/02/2023	Design: Carol Li 03/02/2023
A3 SIZE	Description: ELECTRICAL SCHEMATIC		
 THIRD ANGLE PROJECTION	Part No.: PDU A117BSA23500		REV. 00
	SHEET 2 OF 2	ISSUE DATE: 03/02/2023	