







1. INPUT	
Phase	3-Phase WYE Wiring
Voltage	200-240 Vac / 346-415 Vac, 50/60 Hz
Current	32A (CE, UKCA)
Input Plug	IEC60309(3P+N+E), 6H, 32A
Input Cord	3,000±50mm(4mm²x5C)
2. OUTPUT	
Outlets	{36} IEC60320-C13+ {6} IEC60320-C19
Protection	Circuit breaker - 240Vac/20A, 10KAIC, 1 Pole (6)
3. FEATURES	
Metering	Power metering for input and branch
Switching	N/A
Network Monitoring	HTTPs, SNMP

- NOTE:**
1. All dimension are in millimeters[inches].
 2. Bracket kits to mount are available as options.

		台達電子工業股份有限公司 DELTA ELECTRONICS, INC.	
Drawn: Jackow Chen		Design: Jackow Chen	
A3 SIZE		Description: PHYSICAL DIMENSION	
 THIRD ANGLE PROJECTION	Part No.: PDUA317DSA23500		REV. 00
	SHEET 1 OF 2	ISSUE DATE: 03/21/2023	



NOTE:

1. Please see product documentation for further information.
2. This drawing depicts the line connections and is not representative of the physical layout.

 台達電子工業股份有限公司 DELTA ELECTRONICS, INC.	
Drawn: Carol Li	Design: Carol Li
04/06/2023	04/06/2023
A3 SIZE	Description: ELECTRICAL SCHEMATIC
 THIRD ANGLE PROJECTION	Part No.: PDU A317DSA23500
SHEET 2 OF 2	ISSUE DATE: 04/06/2023
REV. 00	