







1. INPUT	
Phase	3-Phase WYE Wiring
Voltage	100-120 / 173-208 Vac, 50/60 Hz
Current	24A (UL)
Input Plug	NEMA L21-30P
Input Cord	3,000 ±50mm(10AWGx4C)
2. OUTPUT	
Outlets	(42) IEC60320-C13
Protection	Circuit breaker - 240Vac/20A, 10KAIC, 2 Pole (3)
3. FEATURES	
Metering	Power metering for input and branch
Switching	N/A
Network Monitoring	HTTPs, SNMP


- NOTE:
1. All dimension are in millimeters[inches].
 2. Bracket kits to mount are available as options.

		台達電子工業股份有限公司 DELTA ELECTRONICS, INC.	
Drawn: Jackow Chen		Design: Jackow Chen	
A3 SIZE		Description: PHYSICAL DIMENSION	
 THIRD ANGLE PROJECTION	Part No.: PDUA414PEA2B801		REV. 00
	SHEET 1 OF 2		ISSUE DATE: 03/22/2023



NOTE:

1. Please see product documentation for further information.
2. This drawing depicts the line connections and is not representative of the physical layout.

		台達電子工業股份有限公司 DELTA ELECTRONICS, INC.	
Drawn: Carol Li		04/06/2023	Design: Carol Li 04/06/2023
A3 SIZE	Description: ELECTRICAL SCHEMATIC		
 THIRD ANGLE PROJECTION	Part No.: PDU414PEA2B801		REV. 00
	SHEET 2 OF 2	ISSUE DATE: 04/06/2023	