



AlbedoEco Radiant

LED Flat Panel Light

Product Features

- High quality optical PMMA light guide
- High system efficiency up to 115 lm/W
- UGR <19 luminaire ideal for interior lighting
- Single optical system ensures visual comfortable light distribution
- Aluminum frame to ensure optimum heat dissipation
- Uniform indirect light distribution with minimized glare
- Compact interior space application
- Reliable quality, manufacture capability, and global logistics by Delta Group 45-year establishment

Applications



Offices



Commercial





Retail



Healthcare

www.delta-emea.com

 **DELTA**
Smarter. Greener. Together.

	D04PACR64x	D04PACR65x	D04PACR34x	D04PACR35x
Type of Product	Office Lighting Solution			
Lumen Output (lm)	4600	6210	4600	6210
Input Voltage (V)	AC 100 / 277 V			
Power (W)	40	54	40	54
Efficacy (lm/W)	115			
CRI (Ra)	> 80			
CCT (K)	4000 (Other CCT Available: 3000K, 5000K, 6500K)			
Power Factor	> 0.93			
Operating Temp (°C)	-20° C / +40° C			
Product Dimension (mm)	595 x 595 x 11		1195 x 295 x 11	
Lifetime	50.000 hr / L 70			
Warranty	5 Years			
Options	1-10V / Dali / Sensor / Emergency			
Protection	IP20 housing / IP40 optical part / IK03			
Weight (kg)	2			
Dimensions (mm)				
Photometry	 <p>4600 lm 4000K UGR<19</p>			
Remarks	<p>Product Dimension 620 x 620 x 11 mm available on request.</p> 			

Specifications are subject to change without notice.

2016 ver.EN-1.1

Delta Electronics Europe

Zandsteen 15
 2132 MZ Hoofddorp, The Netherlands
 TEL: +31-20-655-0900
 FAX: +31-20-655-0999

For more product information and sales inquiries,
 please contact sleu@delta-europe.com
www.delta-emea.com/ledlighting

