



# Cirrus Troffer

## Architectural recessed LED Troffer

### Product Features

- High quality of light in 3000K CRI 80 (3 steps MacAdam)
- Combined optical system ensures uniform light distribution
- Optimum solution for office working areas
- Fast and simple installation
- On request available in tunable white
- Up to 4 x 14 W linear fluorescent replacement
- Reliable quality, manufacture capability, and global logistics by Delta Group 45-year establishment

### Applications



Offices



Commercial



Library

[www.delta-emea.com](http://www.delta-emea.com)



**DELTA**  
Smarter. Greener. Together.

	D02BAT139W	D02BAT130W	D02BAT140W
Type of Product	Office Lighting Solution		
Lumen Output (lm)	3100	3100	3250
Input Voltage (V)	AC220~240V		
Power (W)	38	32	32
Efficacy (lm/W)	82	97	102
CRI (Ra)	90	80	80
CCT (K)	3000		4000
Power Factor	>0.90		
Operating Temp (°C)	-20 ~ +35		
Dimension	595 x 595 / 622 x 622		
Lifetime	50000 hr / L 80		
Warranty	5 Years		
EEC	A++ / A+ / A		
Weight (kg)	4.5		
Dimensions (mm)			
Photometry			

Specifications are subject to change without notice.

2016 ver.EN-1.0

### Delta Electronics Europe

Zandsteen 15  
 2132 MZ Hoofddorp, The Netherlands  
 TEL: +31-20-655-0900  
 FAX: +31-20-655-0999

For more product information and sales inquiries,  
 please contact [sleu@delta-europe.com](mailto:sleu@delta-europe.com)  
[www.delta-emea.com/ledlighting](http://www.delta-emea.com/ledlighting)

