



# AlbedoEco Radiant

## LED Flat Panel Light

### Product Features

- High quality optical PMMA light guide
- High system efficiency up to 110 lm/W
- UGR <19 luminaire ideal for interior lighting
- Single optical system ensures visual comfortable light distribution
- Aluminum frame to ensure optimum heat dissipation
- Uniform indirect light distribution with minimized glare
- Compact interior space application
- Reliable quality, manufacture capability, and global logistics by Delta Group 49-year establishment

### Applications



Offices



Commercial



Retail



Healthcare

[www.delta-emea.com](http://www.delta-emea.com)



**DELTA**  
Smarter. Greener. Together.

	D04PACR64x	D04PACR65x	D04PACR34x	D04PACR35x
Type of Product	Office Lighting Solution			
Lumen Output (lm)	4400	5940	4400	5940
Input Voltage (V)	AC 220-240V			
Power (W)	40	54	40	54
Efficacy (lm/W)	110 lm/W( UGR<19 )			
CRI (Ra)	> 80			
CCT (K)	4000 (Other CCT Available: 3000K, 5000K, 6500K)			
Power Factor	>0.93			
Operating Temp (°C)	-20 °C / +40 °C			
Product Dimension (mm)	595 x 595 x 11		1195 x 295 x 11	
Lifetime	50.000 hr / L70			
Warranty	5 Years			
Options	1-10V / DALI			
Protection	IP20 housing / IP40 optical part / IK03			
Weight (kg)	3.2			
Dimensions (mm)				
Photometry				
Remarks	Product Dimension 620 x 620 x 11 mm available on request.			

Specifications are subject to change without notice.

All values in +25°C ambient temperature, luminous flux tolerance +-5%, output power tolerance +-5%.

2020/05/01

### Delta Electronics Europe

Zandsteen 15  
 2132 MZ Hoofddorp, The Netherlands  
 TEL: +31-20-655-0900  
 FAX: +31-20-655-0999

For more product information and sales inquiries,  
 please contact [sleu@deltaww.com](mailto:sleu@deltaww.com)  
[www.delta-emea.com/ledlighting](http://www.delta-emea.com/ledlighting)

