

+75°C Staccato

Product Features

- High efficacy up to 147 lm/W
- Replacement for HID and fluorescent fixtures of up to 400W
- Operating temp. range of -40°C to +75°C
- Tempered glass protection
- Lifetime >70,000 hours L80/B10 at Ta 55°C and >50,000 hours L80/B10 at Ta max
- IP66 and IK10 robust protection from dust, water and vandalism
- 0-10V dimming control for the whole product range
- Convenient installation with options for hook, bracket or suspension rope
- Reliable quality, manufacture capability, and global logistics by Delta Group 49-year establishment

Applications



Factory



Warehouse



Industrial




Transport

www.delta-emea.com


 **DELTA**
Smarter. Greener. Together.

	HBExD5G11E	HBExF5G11E	HBExK5G11E
Lumen Output	18,300 lm	22,100 lm	28,000 lm
Input Voltage	AC 220-240 V		
Power	130 W	150 W	200 W
Efficacy (lm/W)	141	147	140
CRI	> Ra 80		
CCT	5,000 K (Other CCT Available: 4,000K)		
Power Factor	≥ 0.9		
Optics	110D / Tempered-Glass		
Operating Temperature	-40°C / +75°C *		
Lifetime	> 70,000 Hrs L80/B10 at Ta 55°C; > 50,000 Hrs L80/B10 at Ta max		
Warranty	5 years		
Mounting	Hook / Wall Mount / Suspension		
Accessories & options	U-Bracket / Y-cable		
Weight	10 kg		

Dimensions (Hook model)



Photometry



Remarks

Lumen output in above table is based on 5000K.
 Product codes and lumen output ranges are subject to change when other CCT applies.
 * Products should be installed at open space with good ventilation.