

Staccato

Product Features

- High efficacy up to 165 lm/W @4000K
- Replacement for HID and fluorescent fixtures of up to 400W
- Operating temp. range of -40°C to +65°C
- IP66 and IK10 robust protection from dust, water and vandalism
- 0-10V and DALI dimming control for the whole product range
- Convenient installation with options for hook, bracket or suspension rope
- Optional diffuser and reflector for glare prevention
- Reliable quality, manufacture capability, and global logistics by Delta Group 49-year establishment

Applications



Factory



Warehouse



Industrial



Transport


www.delta-emea.com




DELTA
Smarter. Greener. Together.

	HBE84xx1E	HBE4xx1E	HBEF4xx1E	HBEK4xx1E	HBE4xx1E
Lumen Output	13,100 lm	18,700 lm	24,700 lm	30,800 lm	40,700 lm
Input Voltage	AC 220-240 V				
Power	85 W	125 W	150 W	200 W	260 W
Efficacy (lm/W)	154	150	165	154	157
CRI	> Ra 80				
CCT	4,000 K (Other CCT Available: 5,000K)				
Power Factor	≥ 0.95				
Optics	100D / 60D / 65D x 100D				
Operating Temperature	-40°C / +65°C				
	Thermal foldback feature reduces lumen output for temperatures above Ta Max				
Lifetime	> 100,000 Hrs L80/B10 at Ta 25°C; > 55,000 Hrs L80/B10 at Ta max				
Warranty	5 years				
Mounting	Hook / Wall Mount / Suspension				
Accessories & options	U-Bracket / Y-cable / Reflector / Diffuser / Tempered-Glass / DALI				
Weight	9 kg				

Dimensions (Hook model)



Photometry



Remarks

Product parameters in above table are based on 100° optics.
Lumen output in above table is based on 4000K.
Product codes and lumen output ranges are subject to change when other CCT applies.

Specifications are subject to change without notice.

2020/04/30