



Fractus

Architectural Recessed LED Downlight

Product Features

- High system efficacy (up to 98 lm/W)
- High quality of light in 4000K CRI 80 (3 steps MacAdam)
- Up to 2 x 42 W compact fluorescent replacement
- Available with Polished, Matt or White reflector
- Available in three different diameters: 166, 216 and 266mm
- IP54-rated version available on request
- Reliable quality, manufacture capability and global logistics by Delta Group 45-year establishment

Applications



Offices



Hotels









Retail



Commercial

www.delta-emea.com

 **DELTA**
Smarter. Greener. Together.

	D02PREP144	D02PREP244	D02PREP344	D02PREP444	D02PREP544
Type of Product	Office Lighting Solution				
Lumen Output (lm)	1350	1850	2350	2850	3250
Input Voltage (V)	AC 220 / 240 V				
Power (W)	15	20	24	29	33
Efficacy (lm/W)	90	93	98	98	98
CRI (Ra)	80				
CCT (K)	4000 (3000 on request)				
Power Factor (%)	> 90				
Operating Temp (°C)	-20° C / +35° C				
Reflector finish	Polished standard (Matt or White on request)				
Lifetime	50.000 hr / L80				
Warranty	5 Years				
Safety standards	IP20 housing and IP40 optical part (IP54 on request)				
Dimension	Ø 166		Ø 216		Ø 266
Dimensions (mm)	 Ø 154 		 Ø 204 		 Ø 254 

Specifications are subject to change without notice.

2015 ver.en-1.1



Delta Electronics Europe

Zandsteen 15
 2132 MZ Hoofddorp, The Netherlands
 TEL: +31-20-655-0900
 FAX: +31-20-655-0999

For more product information and sales inquiries,
 please contact sleu@delta-europe.com
www.delta-emea.com/ledlighting

