



Maha Mega Streetlight

Outdoor Lighting Solutions

Product Features

- High system wattage up to 210 W (110 lm/W)
- Intelligent and step dimming possibilities to meet project requirements
- Up to 13 different optical patterns available on request (PD0 standard)
- Tilttable head over 135° in 5° steps
- Various wattages to replace up to 400 W sodium lamp
- Reliable quality, manufacture capability and global logistics by Delta Group
45-year establishment

Applications



Streets



Industrial



Highways

www.delta-emea.com



DELTA
Smarter. Greener. Together.

	D02MEL100G	D02MEL200G	D02MEL300G
Type of Product	Street Lighting Solution		
Lumen Output (lm)	18250	20100	23000
Input Voltage (V)	AC220~240V		
Power (W)	166	183	209
Efficacy (lm/W)	110		
CRI (Ra)	70		
CCT (K)	4000		
Power Factor	>0.90		
Operating Temp (°C)	-35 °C / +40 °C		
Lens Options	PD0 standard (PDA-PDQ on request)		
Lifetime	100.000 hr / L80		
Warranty	5 Years		
Protection	IP 65 / IK 08		
Weight (kg)	20.1	20.1	20.3
Accessories	Intelligent dimming / Step dimming / DALI		
HPS Replacement	250 W	400 W	
Dimensions (mm)			
Photometry			

Specifications are subject to change without notice.

2016 ver.en-1.2

Delta Electronics Europe

Zandsteen 15
 2132 MZ Hoofddorp, The Netherlands
 TEL: +31-20-655-0900
 FAX: +31-20-655-0999

For more product information and sales inquiries,
 please contact sleu@delta-europe.com
www.delta-emea.com/ledlighting

