



Ridge Troffer

Architectural LED Troffer

Product Features

- High system efficacy up to 94 lm/W
- High quality of light in 3000K CRI 80 (3 steps MacAdam)
- UGR <19 luminaire ideal for interior lighting
- Optimum solution for office working areas
- Available in square and linear version
- Up to 4 x 24 W linear fluorescent replacement
- Reliable quality, manufacture capability, and global logistics by Delta Group 45-year establishment

Applications



Offices



Commercial



Library

www.delta-emea.com



DELTA
Smarter. Greener. Together.

	D02FRES13P	D02FRES14P	D02FREL13P	D02FREL14P
Type of Product	Office Lighting Solution			
Lumen Output (lm)	2850	3000	2950	3100
Input Voltage (V)	AC 220 / 240 V			
Power (W)	32	32	33	33
Efficacy (lm/W)	89	94	89	94
CRI (Ra)	80			
CCT (K)	3000	4000	3000	4000
Power Factor	>0.90			
Operating Temp (°C)	-20° C / +35° C			
Dimension	595 x 595 / 622 x 622		295 x 1195 / 310 x 1245	
Lifetime	50.000 hr / L 80			
Warranty	5 Years			
EEC	A++ / A+ / A			
Weight (kg)	4.3		4.7	
Dimensions (mm)				
Photometry				
	3000lm 4000K UGR<19			

Specifications are subject to change without notice.

2016 ver.en-1.0

Delta Electronics Europe

Zandsteen 15
 2132 MZ Hoofddorp, The Netherlands
 TEL: +31-20-655-0900
 FAX: +31-20-655-0999

For more product information and sales inquiries,
 please contact sleu@delta-europe.com
www.delta-emea.com/ledlighting

