



Ridgy

Architectural LED Troffer

Product Features

- High system efficacy up to 141 lm/W
- UGR <19 luminaire ideal for interior lighting
- High quality of light in 3000K CRI 80 (3 steps MacAdam)
- Versions available for 600x600 and 625x625 ceilings
- Unique optical design with micro prismatic diffuser
- Up to 4 x 24 W linear fluorescent replacement
- Reliable quality, manufacture capability and global logistics by Delta Group 45-year establishment

Applications



Offices



Commercial



Library












Healthcare

www.delta-emea.com



DELTA
Smarter. Greener. Together.

	D02FRNS63P	D02FRNS64P	D02FRNS13P	D02FRNS14P	D02FRNL13P	D02FRNL4P
Type of Product	Office Lighting Solution					
Lumen Output (lm)	3000	3100	4100	4250	4100	4250
Input Voltage (V)	AC 220 / 240 V					
Power (W)	22	22	31	31	31	31
Efficacy (lm/W)	136	141	132	137	132	137
CRI (Ra)	>80					
CCT (K)	3000	4000	3000	4000	3000	4000
Power Factor	>0.90					
Operating Temp (°C)	-20° C / +35° C					
Options	1-10 V / Dali / 3h Emergency					
Lifetime	50000 hr / L 80					
Warranty	5 Years					
Conformity	IEC Class I					
Dimension	595 x 595				295 x 1195	
Dimension (on request)	622 x 622				310 x 1245	
Weight (kg)	3.1				3.3	
Dimensions (mm)	RIDGY - S - 595 x 595 		RIDGY - L - 295 x 1195 			
	RIDGY - S - 622 x 622 (on request) 		RIDGY - L - 310 x 1245 (on request) 			
Photometry			Square recessed 		Linear recessed 	
	4250 lm 4000 K UGR <19		Square surfaced/suspended 		Linear surfaced/suspended 	

Delta Electronics Europe

Zandsteen 15
 2132 MZ Hoofddorp, The Netherlands
 TEL: +31-20-655-0900
 FAX: +31-20-655-0999

For more product information and sales inquiries,
 please contact sleu@delta-europe.com
www.delta-emea.com/ledlighting

Specifications are subject to change without notice.

2016 ver.en-1.0

