

Staccato

Product Features

- High efficacy up to 165 lm/W @4000K
- Replacement for HID and fluorescent fixtures of up to 400W
- Operating temp. range of -40°C to +65°C
- IP66 and IK10 robust protection from dust, water and vandalism
- 0-10V and DALI dimming control for the whole product range
- Convenient installation with options for hook, bracket or suspension rope
- Optional diffuser and reflector for glare prevention
- Reliable quality, manufacture capability, and global logistics by Delta Group 48-year establishment

Applications



Factory



Warehouse



Industrial



Transport


www.delta-emea.com




DELTA
Smarter. Greener. Together.

	HBE84xx1E	HBE4xx1E	HBEF4xx1E	HBEK4xx1E	HBE4xx1E
Lumen Output	13,100 lm	18,700 lm	24,700 lm	30,800 lm	40,700 lm
Input Voltage	AC 220-240 V				
Power	85 W	125 W	150 W	200 W	260 W
Efficacy (lm/W)	154	150	165	154	157
CRI	> Ra 80				
CCT	4,000 K (Other CCT Available: 5,000K)				
Power Factor	≥ 0.95				
Optics	100D / 60D / 65D x 100D / 25D*				
Operating Temperature	-40°C / +65°C				
	Thermal foldback feature reduces lumen output for temperatures above Ta Max				
Lifetime	>100,000 Hrs L80/B10 at Ta=25C; >55,000 Hrs L80B10 at Ta max				
Warranty	5 years				
Mounting	Hook / Wall Mount / Suspension				
Accessories & options	U-Bracket / Y-cable / Reflector / Diffuser / Tempered-Glass / DALI				
Weight	9 kg				

Dimensions (Hook model)



Photometry



Remarks

Product parameters in above table are based on 100° optics.
 Lumen output in above table is based on 4000K.
 Product codes and lumen output ranges are subject to change when other CCT applies.
 *25D version is only available with 150W 19,000lm Staccato.