



# Teshin Radiant LED Tubes

## T5 Replacement Tubes

### Product Features

- High System efficacy (up to 160 lm/W)
- Replacement for traditional T5 tubes
- 180 degrees rotating end cap for best lighting result
- Single end power feed with isolated driver inside to ensure safety
- Uniform light distribution with minimized glare
- Internal driver T6 LED tube with T5 base
- CE certified & VDE pending
- Reliable quality, manufacture capability, and global logistics by Delta Group 45-year establishment

### Applications



Offices



Commercial






Transport



Industrial

[www.delta-emea.com](http://www.delta-emea.com)

 **DELTA**  
Smarter. Greener. Together.

	D04TNxR21x	D04TNxR31x	D04TNxR42x	D04TNxR52x	D04TNxR53x
Product Version	Frosted / Clear				
Lumen Output (lm)	1650 / 1760	2550 / 2720	3000 / 3200	3600 / 3840	4500 / 4800
Input Voltage (V)	AC 100 / 277 V				
Power (W)	11	17	20	24	30
Cover	Frosted or Clear				
CRI (Ra)	> 80				
CCT (K)	4000 (Other CCT Available: 3000K, 5000K, 6500K)				
Power Factor	> 0.95				
Operating Temp (°C)	-20° C / +40° C				
Product Dimension (mm)	22 x 549	22 x 849	22 x 1149	22 x 1449	22 x 1449
Base	G5				
Weight (kg)	0.25	0.35	0.45	0.55	0.55
Lifetime	50.000 hr / L70 / 5 years warranty				
Certifications	CE / RoHS / VDE pending				
Beam Angle	120°				
Dimensions (mm)					
Photometry					
3600 lm 4000K					

Specifications are subject to change without notice.

2016 ver.EN-1.1

### Delta Electronics Europe

Zandsteen 15  
 2132 MZ Hoofddorp, The Netherlands  
 TEL: +31-20-655-0900  
 FAX: +31-20-655-0999

For more product information and sales inquiries,  
 please contact [sleu@delta-europe.com](mailto:sleu@delta-europe.com)  
[www.delta-emea.com/ledlighting](http://www.delta-emea.com/ledlighting)

