


Wall mount

HEC1000PC series

Dimension drawing



Features

- ◆ Reliable and energy efficient thermal solutions.
- ◆ Energy efficient fans and effective compressor.
- ◆ IP55 waterproof at external side.
- ◆ Precise temperature control.
- ◆ Earth-friendly refrigerant.
- ◆ Dry contact alarm output.

Design

- ◆ Slim design.
- ◆ Rated voltage at 48V.
- ◆ Built-in smart controller.
- ◆ High efficiency and reliable fan.
- ◆ Easy installation and maintenance.

Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	796 x 383 x 160 (31.3 x 15.0 x 6.4)
Cooling capacity* _{Note}	W (BTU/hr)	1000 (3400)
Rated voltage	VDC	48
Operating current	A	5.5
Operating voltage range	VDC	42 ~ 58
Operating temperature range	°C	-10 ~ +55
Noise (1.0 meter)	dB-A	55.0
Weight	Kg (Lb)	27 (59.5)

* Note : L35/L35

* Specifications are subject to change without notice.