


Wall / Bottom Mount



Airflow orientation

Features

- ◆ Quick heating
- ◆ Constant Air Flow
- ◆ Compact design
- ◆ High efficiency and reliable DC fan
- ◆ Overheat & short protect function
- ◆ Easy for wall mount or bottom mount


HEH150BA



Dimension drawing

NOTE :

- (1) Material : AL T=1.5mm
- (2) Finish : Powder paint 75~120um, Color 7035
- (3) Dimensional tolerance : $\pm 1.0\text{mm}$



Main feature	Unit	Specification
Outline Dimension	mm (inch)	235H x 185W x 58D (9.3 x 7.3 x 2.3)
Heating Capacity (note 1)	W	1500 \pm 10%
Airflow rate	CFM	67 (typ.)
Rated voltage	VAC	220 (typ.)
Operating voltage range	VAC	180-240
Operating temperature range	°C	-40 ~ +65
Operating current	A	7.2
Acoustic noise at 1M :	dB-A	65 (typ.)
Weight	Kg (lb)	1.5 (3)
Heating element	/	PTC
Ingress Protection rating	IP	IP20 (IEC60529)

Note 1: The heating capacity (w) is @20 °C (68°F) ambient te

2.2835