


**Door mount**

**HET200PC-B series**



Dimension drawing



UNIT:MM

Features

- ◆ IP55 waterproof at external side
- ◆ FAN / TEC / Control fail alarm
- ◆ Clear LED status indicator
- ◆ Standalone temperature control
- ◆ High efficiency and reliable fan modules

Design

- ◆ High efficiency of cooling & Heating
- ◆ Thermal electric cooling module
- ◆ Rated voltage at 48V
- ◆ Built-in controller

Main feature	Unit	Model Number
		HET200PC-B
Outline dimension	mm	400 H x 181 W x 143 D
Weight	Kg	6.0± 0.5
Cooling capacity (ΔT =0 °C)	W	200
Heating capacity @-40° C	W	225
Rated voltage	VDC	48 (TYP.)
Operating voltage range	VDC	40-56
Actually Current	A	6.1 (TYP.)
Power Consumption	W	293
Operating temperature	°C	-40-55
Internal airflow rate	CFM	85 (TYP.)
External airflow rate		135 (TYP.)
Acoustic noise at 1M :	dB-A	65.0 dB-A(Typ.)
(Sound pressure)		69.0(max.)

\* Specifications are subject to change without notice.