



Internal door mount



Features


- ♦ IP55 waterproof at external side
- ◆ Dry contact alarm output

Design

- ◆ Air to air heat exchange
- ♦ Rated voltage at 24V
- Reduntant fan quantity design
- ♦ High efficiency and reliable fan
- Easy installation and maintenance

HEX010VA series

Dimension drawing



Main feature	Unit	Specification
Dimension (H x W x D)	mm (inch)	415 x 275 x 65 (16 x 11 x 2.6)
Cooling capacity _{*Note}	W/K (W/°F)	10 (6)
Rated voltage	VDC	24
Operating current	Α	1.2
Opearting power	w	29
Operating voltage range	VDC	20 ~ 26
Operating temperature range	°C	-10 ~ +65
Noise (1.5 meter)	dB-A	61.0
Weight	Kg (Lb)	4 (9)

^{*} Note : The cooling capacity (W/K , W/°C or W/°F) is defined as $\,$ Q/ $(T_{I^{\!-}}T_{A})$

Q : Heat dissipation (W) from inside of cabinet

T₁: Return temperature of internal air circuit (K, °C or °F)

 T_A : Ambient temperature of external air circuit (K , °C or °F)

^{*} Specifications are subject to change without notice.