



Internal door mount



Features


- ♦ Slim Dimension.(only 100mm Depth)
- **♦** IP55 waterproof at external side.
- **♦** Standalone temperature control.
- **♦** RS-485 function (Optional).
- Dry contact alarm output.
- ◆ Clear LED status indicator.

Design

- **♦** Rated voltage at 48V.
- **♦** Built-in smart controller.
- **♦** High efficiency and reliable fan.
- **♦** Easy installation and maintenance.

HEX070PB

Dimension drawing



Main feature	Unit	Specification
Dimension (H x W x D) (Doesn't contain flange)	mm (inch)	900 x 450 x 100 (35.4 x 17.7 x 3.9)
Cooling capacity	W/K	70
Rated voltage	VDC	48
Operating current	Α	3.8
Operating power	W	182
Operating voltage range	VDC	40 ~ 60
Operating temperature range	°C	-10 ~ +65
Noise (1.5 meter)	dB-A	62.0
Weight	Kg (Lb)	17.5 (38.5)

^{*} Specifications are subject to change without notice.