




Internal Door mount



HEX080PD series

Dimension drawing



Features

- IP55 waterproof at external side
- Standalone temperature control
- RS-485 function
- Clear LED status indicator
- Dry contact alarm output

Design

- Air to air heat exchange
- Rated voltage at 48V
- High efficiency and reliable fan
- Easy installation and maintenance

Main feature Specification Unit 950 x 450 x 150 mm Dimension (H x W x D) (37 x 18 x 6) (in) Cooling capacity*Note W/K (W/°F) 80 (44) 48 **Rated voltage** VDC 2.2 **Operating current** Α **Opearting power** W 106 Operating voltage range 40 ~ 60 VDC °C -10 ~ +65 Operating temperature range Noise (1.5 meter) dB-A 65.0 Weight Kg (Lb) 19 (42)

* Note : The cooling capacity (W/K , W/°C or W/°F) is defined as $Q/(T_I-T_A)$

Q : Heat dissipation (W) from inside of cabinet

- T_I : Return temperature of internal air circuit (K , °C or °F)
- T_A : Ambient temperature of external air circuit (K , °C or °F)

* Specifications are subject to change without notice.